

SERIES 68FV

SOLID POLYAMIDE 6 WHEELS



Wheel description

Solid polyamide 6 wheels.

Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing, with ball bearing and with ball bearing facilities.

Diameters: 80-250 mm

Carrying capacity: 150-1000 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

Uses

Environments

Suitable for applications in humid environments, where medium-harsh chemicals are present.

Usage temperatures: from 30°C to 130°C

Floors



Handling

