

SERIES 62GH

“TR-ROLL” POLYURETHANE WHEELS, CAST IRON CENTER



Wheel description

Ruota in poliuretano “TR-ROLL”, durezza 75 Shore A, ottime caratteristiche di scorrevolezza ed elasticità, buona resistenza ad usura e lacerazione. Nucleo in alluminio pressofuso.

Hub

The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

Diameters: 200-400 mm

Carrying capacity: 800-1700 daN

Fittings with swivel, fixed and swivel with brake brackets



Electrowelded brackets EE MHD

Max. carrying capacity 800 daN – available diameters 200 mm
Top plate fastening. Adjustable rear-locking brake systems



Electrowelded brackets EE HD

Max. carrying capacity 1400 daN – available diameters 200-300 mm
Top plate fastening. Adjustable rear-locking brake systems



Supporti elettrosaldati tipo EE EHD

Max. carrying capacity 1700 daN – available diameters 400 mm
Top plate fastening. Adjustable rear-locking brake systems

Uses

Environments

The series is suitable for use in industrial environments for carrying medium-heavy loads, including with mixed outdoor-indoor use. Can be used at speeds of up to 16 km/h; possibility of using for mechanised towing. Typical usage: trolleys for automotive industry. *Usage temperatures:* from -20 °C to +70 °C

Floors



Handling

