

SERIES 65ER

“TR” POLYURETHANE WHEELS WITH ERGONOMIC ROUND PROFILE AND ALUMINIUM CENTER



Wheel description

Very thick “TR” polyurethane with ergonomic round profile, hardness 95 Shore A, excellent rolling resistance and elasticità, good resistance to wear and tear; cast aluminium center

Hub

The housing is obtained by moulding and contains ball bearings series Z. The hub is available also without bearings.

Diametri disponibili: 125-200 mm

Portate: 450-800 daN

Fittings with swivel, fixed and swivel with brake brackets



Supporti medi tipo M

Max. carrying capacity 500 daN – available diameters 160-200 mm
Top plate fastening. Adjustable front-locking brake



Supporti pesanti tipo P

Max. carrying capacity 750 daN – available diameters 125-200 mm
Top plate fastening. Front-locking and adjustable rear-locking brake systems



Supporti extra-pesanti tipo EP

Max. carrying capacity 1600 daN – available diameters 160-200 mm
Top plate fastening. Adjustable rear-locking brake systems



Supporti elettrosaldati tipo EE MHD

Max. carrying capacity 900 daN – available diameters 125-200 mm
Top plate fastening. Adjustable rear-locking brake systems

Uses

Environments

The ergonomic round profile reduces the start-up coefficient when the castors are positioned at 90° from the line of movement and therefore reduces the amount of effort required when handling trolleys. Combined with appropriate brackets, they guarantee excellent performances for mechanical handling up to 12 km/h. *Usage temperatures:* from -20 °C to +80 °C

Floors



Handling

