


FILO OVALE / OVAL WIRE / OVAL DRAHT / FIL OVALE

ESEMPIO D'ORDINE / ORDERING EXAMPLE / BESTELLBEISPIEL / EXAMPLE DE COMMANDE: (25) MHR 19 - 051
CONSEGNA DA MAGAZZINO / DELIVERY FROM STOCK / LIEFERUNG AB LAGER / DISPONIBLE SUR STOCK

D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R	A		B		C		D	
					20% L ₀		25% L ₀		37% L ₀		f _b	
mm	mm	mm		N / mm	N	mm	N	mm	N	mm	N	mm
9.5	4.7	25	MHR 10 - 025	17.7	89	5.0	112	6.3	165	9.3	181	10.2
		32	MHR 10 - 032	15.2	97	6.4	122	8.0	179	11.8	216	14.2
		38	MHR 10 - 038	13.2	100	7.6	125	9.5	186	14.1	222	16.8
		44	MHR 10 - 044	11.3	99	8.8	124	11.0	184	16.3	219	19.4
		51	MHR 10 - 051	8.4	86	10.2	108	12.8	159	18.9	197	23.4
		64	MHR 10 - 064	7.2	92	12.8	115	16.0	171	23.7	203	28.2
		76	MHR 10 - 076	5.8	88	15.2	110	19.0	163	28.1	198	34.2
		305	MHR 10 - 305	1.5	91	61.0	114	76.3	169	112.9	201	133.8
13	7	25	MHR 13 - 025	30.4	152	5.0	192	6.3	283	9.3	362	11.9
		32	MHR 13 - 032	22.1	141	6.4	177	8.0	261	11.8	358	16.2
		38	MHR 13 - 038	19.1	145	7.6	181	9.5	269	14.1	357	18.7
		44	MHR 13 - 044	16.1	142	8.8	177	11.0	262	16.3	343	21.3
		51	MHR 13 - 051	15.0	153	10.2	192	12.8	284	18.9	384	25.6
		64	MHR 13 - 064	11.8	151	12.8	189	16.0	280	23.7	382	32.4
		76	MHR 13 - 076	9.8	149	15.2	186	19.0	275	28.1	382	39.0
		89	MHR 13 - 089	8.1	144	17.8	181	22.3	266	32.9	372	45.9
		102	MHR 13 - 102	6.3	129	20.4	161	25.5	238	37.7	329	52.3
305	MHR 13 - 305	2.1	128	61.0	160	76.3	237	112.9	320	152.5		
16	8.7	25	MHR 16 - 025	56.8	284	5.0	358	6.3	528	9.3	596	10.5
		32	MHR 16 - 032	38.2	244	6.4	306	8.0	451	11.8	504	13.2
		38	MHR 16 - 038	33.3	253	7.6	316	9.5	470	14.1	573	17.2
		44	MHR 16 - 044	29.2	257	8.8	321	11.0	476	16.3	566	19.4
		51	MHR 16 - 051	25.5	260	10.2	326	12.8	482	18.9	617	24.2
		64	MHR 16 - 064	19.6	251	12.8	314	16.0	464	23.7	572	29.2
		76	MHR 16 - 076	16.2	246	15.2	308	19.0	455	28.1	588	36.3
		89	MHR 16 - 089	13.7	244	17.8	306	22.3	451	32.9	571	41.7
		102	MHR 16 - 102	12.7	259	20.4	324	25.5	479	37.7	621	48.9
		115	MHR 16 - 115	10.3	237	23.0	297	28.8	439	42.6	547	53.1
305	MHR 16 - 305	3.9	238	61.0	298	76.3	440	112.9	552	141.6		
19.5	9.5	25	MHR 19 - 025	99.0	495	5.0	624	6.3	921	9.3	1069	10.8
		32	MHR 19 - 032	77.5	496	6.4	620	8.0	915	11.8	1077	13.9
		38	MHR 19 - 038	55.9	425	7.6	531	9.5	788	14.1	956	17.1
		44	MHR 19 - 044	50.0	440	8.8	550	11.0	815	16.3	980	19.6
		51	MHR 19 - 051	42.2	430	10.2	540	12.8	798	18.9	945	22.4
		64	MHR 19 - 064	33.3	426	12.8	533	16.0	789	23.7	949	28.5
		76	MHR 19 - 076	25.0	380	15.2	475	19.0	703	28.1	838	33.5
		89	MHR 19 - 089	23.1	411	17.8	515	22.3	760	32.9	929	40.2
		102	MHR 19 - 102	20.6	420	20.4	525	25.5	777	37.7	937	45.5
		115	MHR 19 - 115	18.6	428	23.0	536	28.8	792	42.6	936	50.3
		127	MHR 19 - 127	17.7	450	25.4	563	31.8	832	47.0	1002	56.6
		140	MHR 19 - 140	16.2	454	28.0	567	35.0	839	51.8	1003	61.9
		152	MHR 19 - 152	13.9	423	30.4	528	38.0	781	56.2	940	67.6
305	MHR 19 - 305	6.4	390	61.0	488	76.3	723	112.9	872	136.3		

Note: 1 N = 0,102 Kg (force)

D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	R N / mm	A		B		C		D	
					20% L ₀		25% L ₀		37% L ₀		f _b	
mm	mm	mm			N	mm	N	mm	N	mm	N	mm
25.5	13	25	MHR 26 - 025	137.3	687	5.0	865	6.3	1277	9.3	1359	9.9
		32	MHR 26 - 032	105.9	678	6.4	847	8.0	1250	11.8	1408	13.3
		38	MHR 26 - 038	88.3	671	7.6	839	9.5	1245	14.1	1457	16.5
		44	MHR 26 - 044	76.5	673	8.8	842	11.0	1247	16.3	1476	19.3
		51	MHR 26 - 051	63.7	650	10.2	815	12.8	1204	18.9	1401	22.0
		64	MHR 26 - 064	49.0	627	12.8	784	16.0	1161	23.7	1343	27.4
		76	MHR 26 - 076	41.7	634	15.2	792	19.0	1172	28.1	1368	32.8
		89	MHR 26 - 089	35.8	637	17.8	798	22.3	1178	32.9	1396	39.0
		102	MHR 26 - 102	31.9	651	20.4	813	25.5	1203	37.7	1426	44.7
		115	MHR 26 - 115	27.0	621	23.0	778	28.8	1150	42.6	1345	49.8
		127	MHR 26 - 127	24.5	622	25.4	779	31.8	1152	47.0	1379	56.3
		140	MHR 26 - 140	22.6	633	28.0	791	35.0	1171	51.8	1424	63.0
		152	MHR 26 - 152	19.6	596	30.4	745	38.0	1102	56.2	1298	66.2
178	MHR 26 - 178	17.7	630	35.6	788	44.5	1166	65.9	1379	77.9		
203	MHR 26 - 203	15.7	637	40.6	798	50.8	1179	75.1	1389	88.5		
305	MHR 26 - 305	10.8	659	61.0	824	76.3	1219	112.9	1475	136.6		
32	16	38	MHR 32 - 038	196.1	1490	7.6	1863	9.5	2765	14.1	3157	16.1
		44	MHR 32 - 044	176.5	1553	8.8	1942	11.0	2877	16.3	3265	18.5
		51	MHR 32 - 051	147.1	1500	10.2	1883	12.8	2780	18.9	3148	21.4
		64	MHR 32 - 064	107.9	1381	12.8	1726	16.0	2557	23.7	2956	27.4
		76	MHR 32 - 076	90.2	1371	15.2	1714	19.0	2535	28.1	2950	32.7
		89	MHR 32 - 089	74.5	1326	17.8	1661	22.3	2451	32.9	2913	39.1
		102	MHR 32 - 102	64.7	1320	20.4	1650	25.5	2439	37.7	2808	43.4
		115	MHR 32 - 115	55.9	1286	23.0	1610	28.8	2381	42.6	2778	49.7
		127	MHR 32 - 127	47.1	1196	25.4	1498	31.8	2214	47.0	2548	54.1
		140	MHR 32 - 140	44.1	1235	28.0	1544	35.0	2284	51.8	2646	60.0
		152	MHR 32 - 152	40.7	1237	30.4	1547	38.0	2287	56.2	2719	66.8
		178	MHR 32 - 178	34.3	1221	35.6	1526	44.5	2260	65.9	2682	78.2
		203	MHR 32 - 203	31.4	1275	40.6	1595	50.8	2358	75.1	2738	87.2
254	MHR 32 - 254	22.1	1123	50.8	1403	63.5	2077	94.0	2438	110.3		
305	MHR 32 - 305	20.6	1257	61.0	1572	76.3	2326	112.9	2748	133.4		
38.5	19.5	51	MHR 38 - 051	178.5	1821	10.2	2285	12.8	3374	18.9	3838	21.5
		64	MHR 38 - 064	132.4	1695	12.8	2118	16.0	3138	23.7	3482	26.3
		76	MHR 38 - 076	107.9	1640	15.2	2050	19.0	3032	28.1	3582	33.2
		89	MHR 38 - 089	94.1	1675	17.8	2098	22.3	3096	32.9	3764	40.0
		102	MHR 38 - 102	82.4	1681	20.4	2101	25.5	3106	37.7	3683	44.7
		115	MHR 38 - 115	73.7	1695	23.0	2123	28.8	3140	42.6	3692	50.1
		127	MHR 38 - 127	62.8	1595	25.4	1997	31.8	2952	47.0	3467	55.2
		140	MHR 38 - 140	58.8	1646	28.0	2058	35.0	3046	51.8	3604	61.3
		152	MHR 38 - 152	52.0	1581	30.4	1976	38.0	2922	56.2	3515	67.6
		178	MHR 38 - 178	44.1	1570	35.6	1962	44.5	2906	65.9	3493	79.2
		203	MHR 38 - 203	37.3	1514	40.6	1895	50.8	2801	75.1	3346	89.7
		254	MHR 38 - 254	31.4	1595	50.8	1994	63.5	2952	94.0	3548	113.0
		305	MHR 38 - 305	24.5	1495	61.0	1869	76.3	2766	112.9	3398	138.7
51	25.5	64	MHR 51 - 064	210.8	2698	12.8	3373	16.0	4996	23.7	5755	27.3
		76	MHR 51 - 076	171.6	2608	15.2	3260	19.0	4822	28.1	5337	31.1
		89	MHR 51 - 089	142.2	2531	17.8	3171	22.3	4678	32.9	5432	38.2
		102	MHR 51 - 102	119.6	2440	20.4	3050	25.5	4509	37.7	5203	43.5
		115	MHR 51 - 115	107.9	2482	23.0	3108	28.8	4597	42.6	5212	48.3
		127	MHR 51 - 127	100.0	2540	25.4	3180	31.8	4700	47.0	5510	55.1
		140	MHR 51 - 140	90.2	2526	28.0	3157	35.0	4672	51.8	5538	61.4
		152	MHR 51 - 152	84.3	2563	30.4	3203	38.0	4738	56.2	5690	67.5
		178	MHR 51 - 178	71.1	2531	35.6	3164	44.5	4685	65.9	5624	79.1
		203	MHR 51 - 203	61.8	2509	40.6	3139	50.8	4641	75.1	5513	89.2
		254	MHR 51 - 254	49.5	2515	50.8	3143	63.5	4653	94.0	5603	113.2
		305	MHR 51 - 305	43.1	2629	61.0	3289	76.3	4866	112.9	6181	143.4
		63	38	76	MHR 63 - 076	300.1	4562	15.2	5702	19.0	8433	28.1
89	MHR 63 - 089			240.3	4277	17.8	5359	22.3	7906	32.9	8675	36.1
102	MHR 63 - 102			211.8	4321	20.4	5401	25.5	7985	37.7	9298	43.9
115	MHR 63 - 115			188.3	4331	23.0	5423	28.8	8022	42.6	9114	48.4
127	MHR 63 - 127			162.8	4135	25.4	5177	31.8	7652	47.0	8987	55.2
140	MHR 63 - 140			156.9	4393	28.0	5491	35.0	8127	51.8	9555	60.9
152	MHR 63 - 152			147.1	4472	30.4	5590	38.0	8267	56.2	9709	66.0
178	MHR 63 - 178			108.9	3877	35.6	4846	44.5	7177	65.9	8374	76.9
203	MHR 63 - 203			94.1	3820	40.6	4780	50.8	7067	75.1	8158	86.7
229	MHR 63 - 229			86.3	3953	45.8	4945	57.2	7310	84.7	8544	99.0
254	MHR 63 - 254			75.5	3835	50.8	4794	63.5	7097	94.0	8471	112.2
305	MHR 63 - 305			64.7	3947	61.0	4937	76.3	7305	112.9	8599	132.9

