


Molle carico extra-forte  
Extra-heavy load springs  
Federn für höchste belastung  
Ressorts charge extra-forte

Serie  
Series  
Serie  
Série

**G**

ISO 10243



D <sub>H</sub>	D <sub>d</sub>	L <sub>0</sub>	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	Rigidità Rate Rigidez Raideur	17%		20%		25%		D			
					3.000.000		1.500.000		Max. Defl.		Approx.			
b x h				N / mm	mm	N	mm	N	mm	N	mm	N		
10	5	25	G 10 - 025	36.8	4.3	158	5.0	184	6.3	232	7.7	283		
		32	G 10 - 032	27.9	5.4	151	6.4	179	8.0	223	10.6	296		
		38	G 10 - 038	23.7	6.5	154	7.6	180	9.5	225	12.6	299		
		44	G 10 - 044	19.2	7.5	144	8.8	169	11.0	211	13.8	265		
		51	G 10 - 051	16.5	8.7	144	10.2	168	12.8	211	16.2	267		
		64	G 10 - 064	13.2	10.9	144	12.8	169	16.0	211	20.4	269		
		76	G 10 - 076	10.9	12.9	141	15.2	166	19.0	207	25.2	275		
1.9 x 1.6		305	G 10 - 305	2.6	51.9	135	61.0	159	76.3	198	110.8	288		
12.5	6.3	25	G 13 - 025	58.5	4.3	252	5.0	293	6.3	369	8.1	474		
		32	G 13 - 032	43.9	5.4	237	6.4	281	8.0	351	9.9	435		
		38	G 13 - 038	36.0	6.5	234	7.6	274	9.5	342	12.9	464		
		44	G 13 - 044	30.3	7.5	227	8.8	267	11.0	333	14.1	427		
		51	G 13 - 051	26.2	8.7	228	10.2	267	12.8	335	17.4	456		
		64	G 13 - 064	21.2	10.9	231	12.8	271	16.0	339	21.0	445		
		76	G 13 - 076	17.1	12.9	221	15.2	260	19.0	325	26.4	451		
		89	G 13 - 089	14.5	15.1	219	17.8	258	22.3	323	31.5	457		
2.6 x 2.0		102	G 13 - 102	12.7	17.3	220	20.4	259	25.5	324	36.0	457		
		305	G 13 - 305	4.3	51.9	223	61.0	262	76.3	328	111.3	479		
16	8	25	G 16 - 025	118	4.3	507	5.0	590	6.3	743	8.5	1003		
		32	G 16 - 032	89.0	5.4	481	6.4	570	8.0	712	11.0	979		
		38	G 16 - 038	72.1	6.5	469	7.6	548	9.5	685	13.2	952		
		44	G 16 - 044	60.9	7.5	457	8.8	536	11.0	670	14.7	895		
		51	G 16 - 051	52.3	8.7	455	10.2	533	12.8	669	17.7	926		
		64	G 16 - 064	41.2	10.9	449	12.8	527	16.0	659	21.9	902		
		76	G 16 - 076	34.1	12.9	440	15.2	518	19.0	648	27.8	948		
		89	G 16 - 089	29.5	15.1	445	17.8	525	22.3	658	31.2	920		
		3.2 x 2.9		102	G 16 - 102	25.6	17.3	443	20.4	522	25.5	653	37.9	970
				115	G 16 - 115	22.4	19.6	439	23.0	515	28.8	645	44.5	997
		305	G 16 - 305	8.4	51.9	436	61.0	512	76.3	641	113.5	953		
20	10	25	G 20 - 025	293	4.3	1260	5.0	1465	6.3	1846	6.9	2022		
		32	G 20 - 032	224	5.4	1210	6.4	1434	8.0	1792	9.4	2106		
		38	G 20 - 038	177	6.5	1151	7.6	1345	9.5	1682	12.0	2124		
		44	G 20 - 044	149	7.5	1118	8.8	1311	11.0	1639	13.5	2012		
		51	G 20 - 051	128	8.7	1114	10.2	1306	12.8	1638	16.2	2074		
		64	G 20 - 064	99.0	10.9	1079	12.8	1267	16.0	1584	21.2	2099		
		76	G 20 - 076	81.7	12.9	1054	15.2	1242	19.0	1552	24.7	2018		
		89	G 20 - 089	69.5	15.1	1049	17.8	1237	22.3	1550	28.8	2002		
		4.1 x 3.8		102	G 20 - 102	60.6	17.3	1048	20.4	1236	25.5	1545	34.8	2109
				115	G 20 - 115	53.0	19.6	1039	23.0	1219	28.8	1526	39.0	2067
				127	G 20 - 127	47.5	21.6	1026	25.4	1207	31.8	1511	43.0	2043
				139	G 20 - 139	43.0	23.8	1023	28.0	1204	35.0	1505	45.3	1948
				152	G 20 - 152	39.0	25.8	1006	30.4	1186	38.0	1482	50.4	1966
		305	G 20 - 305	21.2	51.9	1100	61.0	1293	76.3	1618	103.5	2194		

Note: 1 N = 0,102 Kg (force)

